

# Capac de inchidere CV-PK-3-B

Numar piesa: 6213

FESTO



## Fisa de date

| Caracteristica                              | Valoare                                                                                          |
|---------------------------------------------|--------------------------------------------------------------------------------------------------|
| Unitate de ambalare                         | 10                                                                                               |
| Presiune de lucru in functie de temperatura | -0.095 MPa...1 MPa<br>-0.95 bar...10 bar<br>-13.775 psi...145 psi                                |
| Mediu de operare                            | Aer comprimat conform ISO 8573-1:2010 [7:-:-]                                                    |
| Conformitatea LABS                          | VDMA24364-B2-L                                                                                   |
| Temperatura ambianta                        | -10 °C...80 °C                                                                                   |
| Conector pneumatic 1                        | pentru furtun cu Ø exterior 4 mm<br>pentru niplu de legatura Ø interior 3 mm cu piulita olandeza |
| Nota privind materialele                    | Conform RoHS                                                                                     |
| Material capac                              | TPE-U (PU)                                                                                       |