

Capac de inchidere CV-PK-4-B

Numar piesa: 6214

FESTO



Fisa de date

Caracteristica	Valoare
Unitate de ambalare	10
Presiune de lucru in functie de temperatura	-0.095 MPa...1 MPa -0.95 bar...10 bar -13.775 psi...145 psi
Mediu de operare	Aer comprimat conform ISO 8573-1:2010 [7:-:-]
Conformitatea LABS	VDMA24364-B2-L
Temperatura ambianta	-10 °C...80 °C
Conector pneumatic 1	pentru furtun cu Ø exterior 6 mm pentru niplu de legatura Ø interior 4 mm cu piulita olandeza
Nota privind materialele	Conform RoHS
Material capac	TPE-U (PU)