


Supapa evacuare rapida SEU-3/8

Numar piesa: 6755

FESTO



Fisa de date

Caracteristica	Valoare
Functie de ventil	Exhaustare rapida
Selectare functie suplimentara	cu amortizor de zgomot
Conector pneumatic 1	G3/8
Conexiune pneumatica 2	G3/8
Tipul de montare	insurubabil
Debit nominal normal de aerisire 0,6->0,5 MPa (6->5 bari, 87->72,5 psi)	2280 l/min
Debit normal ventilare 0,6->0 MPa (6->0 bari, 87->0 psi)	4680 l/min
Debit nominal normal de ventilare 0,6->0,5 MPa (6->5 bari, 87->72,5 psi)	2880 l/min
Presiune de lucru	0.2 bar...10 bar
Temperatura ambianta	-20 °C...75 °C
Material carcasa	Aluminiu turnat sub presiune
Mediu de operare	Aer comprimat conform ISO 8573-1:2010 [7:...]
Latimea nominala	11 mm
Pozitie de instalare	orice
Nota referitoare la mediul de lucru/comanda	Posibilitatea operarii cu ulei (necesar pentru operare ulterioara)
Conformitatea LABS	VDMA24364-B1/B2-L
Temperatura medie	-20 °C...75 °C
Nivel de presiune acustica	83 dB(A)
Greutate produs	160 g
Material garnituri	NBR