


Ventil cu tacher V-3-1/4-B

Numar piesa: 6808

FESTO



Fisa de date

Caracteristica	Valoare
Functie de ventil	3/2 normal inchis monostabil
Tip de actionare	mecanic
Debit nominal standard (normalizat conform DIN 1343)	600 l/min
Racord pneumatic de lucru	G1/4
Presiune de lucru	-0.95 bar...10 bar
Structura constructiva	Scaun-farfurie
Latimea nominala	7 mm
Tipul de comanda	direct
Protectie la explozie	Zona 1 (ATEX) Zona 2 (ATEX) Zona 21 (ATEX) Zona 22 (ATEX)
Conformitatea LABS	VDMA24364-B1/B2-L
Temperatura ambianta	-10 °C...60 °C
Fora de actionare	70 N
Greutate produs	130 g
Tipul de montare	cu orificiu de trecere
Conector pneumatic 1	G1/4
Conexiune pneumatica 2	G1/4
Conector pneumatic 3	G1/4
Material garnituri	NBR
Material carcasa	Aluminiu turnat sub presiune