

Amortizor de zgomot U-1/8-B

Numar piesa: 6841

FESTO



Fisa de date

Caracteristica	Valoare
Pozitie de instalare	orice
Presiune de functionare interval complet de temperatura	0 MPa...1 MPa 0 bar...10 bar 0 psi...145 psi
Debit in raport cu atmosfera	1340 l/min
Mediu de operare	Aer comprimat conform ISO 8573-1:2010 [7:-:-]
Nota referitoare la mediul de lucru/comanda	Este posibila functionarea cu ulei
Clasa de rezistenta la coroziune KBK	1 - stres redus la coroziune
Conformitatea LABS	VDMA24364-B1/B2-L
Nivel de presiune acustica	74 dB(A)
Temperatura ambianta	-10 °C...70 °C
Greutate produs	8 g
Conexiune pneumatica	G1/8
Material insertie amortizor de zgomot	PE
Material pivot de insurubare	Aluminiu
Nota privind materialele	Conform RoHS
Material carcasa	Aluminiu