


Ventil cu parghie si buton H-4/3-M5

Numar piesa: 7334

FESTO



Fisa de date

Caracteristica	Valoare
Functie de ventil	4/3 ventilat
Tip de actionare	manual
Debit nominal standard (normalizat conform DIN 1343)	125 l/min
Racord pneumatic de lucru	M5
Presiune de lucru	0 bar...8 bar
Tip de revenire	arc mecanic
Latimea nominala	4 mm
Principiul de etansare	slab
Tipul de comanda	pilotat
Directia de curgere	nu este reversibil
Conformitatea LABS	VDMA24364-B1/B2-L
Conector pneumatic 1	M5
Conexiune pneumatica 2	M5
Conector pneumatic 3	necontorizat