

Racord L NPFC-L-R18-G18-MF

Numar piesa: 8030216

FESTO



Fisa de date

Caracteristica	Valoare
Material racord filetat	Alama, nichelata
Unitate de ambalare	10
Presiune de lucru	-0.95 bar...50 bar
Mediu de operare	Aer comprimat conform ISO 8573-1:2010 [:-:~:-]
Clasa de rezistenta la coroziune KBK	1 - stres redus la coroziune
Conformitatea LABS	VDMA24364-B1/B2-L
Temperatura ambianta	-20 °C...150 °C
Greutate produs	19.8 g
Conector pneumatic 1	R1/8
Conexiune pneumatica 2	G1/8
Nota privind materialele	Conform RoHS