

Portal planar YXCF-3

Numar piesa: 8032547

FESTO



Fisa de date

Caracteristica	Valoare
Planeitatea necesara a suprafetelor de cultivare	0.1 mm/m
Paralelismul necesar al suprafetelor cultivate	0.1 mm/m
Pozitie de instalare	orizontala
Structura constructiva	Sistem de portaluri zonale cu module de actionare electrica
Ciclu de lucru	100%
Conformitatea LABS	VDMA24364 zona III
Temperatura de depozitare	-20 °C...60 °C
Umiditate relativa	0 - 90 %
Temperatura ambianta	5 °C...45 °C
Interval de intretinere	2500 km
Nota privind materialele	Conform RoHS
Material placa de adaptare	Aluminiu, anodizat Otel, acoperit
Material echer de fixare	Otel inoxidabil aliaj inalt
Material lanturi energetice	Ranforsat cu PA