

Tub plastic PAN-R-22X2-SW

Numar piesa: 8036207

FESTO



Fisa de date

Caracteristica	Valoare
Ø exterior	22 mm
raza de indoire relevanta pentru debit	350 mm
Ø interior	18 mm
Presiune de functionare interval complet de temperatura	-0.095 MPa...0.8 MPa -0.95 bar...8 bar -13.775 psi...116 psi
Presiune de lucru in functie de temperatura	-0.095 MPa...1.4 MPa -0.95 bar...14 bar -13.775 psi...203 psi
Mediu de operare	Aer comprimat conform ISO 8573-1:2010 [7:-:-]
Conformitatea LABS	VDMA24364-B2-L
Temperatura ambianta	-30 °C...80 °C
Greutatea produsului in functie de lungime	0.131 kg/m
Conexiune pneumatica	pentru conector cu Ø exterior 22 mm
Culoare	negru
Duritate Shore	D 62 +/-3
Nota privind materialele	Conform RoHS
Material furtun	TPE-A