

Bobina
VACC-S18-120-A1-1
Numar piesa: 8040580

FESTO



Fisa de date

Caracteristica	Valoare
Tip de actionare	electric
Pozitie de instalare	orice
Indicatorul pozitiei de comutare	nu
Ciclu de lucru	100%
Clasa de izolare	H
Caracteristici bobina	24 V CC: 12,0 W
Fluctuatii de tensiune admise	-15 % / +10 %
Clasa de rezistenta la coroziune KBK	4 - Mediu coroziv deosebit de puternic
Conformitatea LABS	VDMA24364 zona III
Tip de protectie	IP65
Temperatura ambianta	-20 °C...60 °C
Greutate produs	530 g
Conector electric	Forma A Stecker conform EN 175301-803
Nota privind materialele	Conform RoHS
Material bobina	PA Otel