

Ventil cu rola unisens VAOM-R4-20-D2-52

Numar piesa: 8049236

FESTO



Fisa de date

Caracteristica	Valoare
Latime	20 mm
Tip de actionare	mecanic
Pozitie de instalare	Nivel de miscare
Structura constructiva	Ventil cu rola unisens
Tipul de comanda	direct
Clasa de rezistenta la coroziune KBK	1 - stres redus la coroziune
Conformitatea LABS	VDMA24364-B1/B2-L
Temperatura ambianta	-10 °C...60 °C
Tipul de montare	insurubat fix
Nota privind materialele	Conform RoHS
Material sistem de actionare	Otel galvanizat