

# Ventil cu rola unisens VAOM-R4-20-D2-32

Numar piesa: 8049237

FESTO



## Fisa de date

| Caracteristica                       | Valoare                      |
|--------------------------------------|------------------------------|
| Latime                               | 20 mm                        |
| Tip de actionare                     | mecanic                      |
| Pozitie de instalare                 | Nivel de miscare             |
| Structura constructiva               | Ventil cu rola unisens       |
| Tipul de comanda                     | direct                       |
| Clasa de rezistenta la coroziune KBK | 1 - stres redus la coroziune |
| Conformitatea LABS                   | VDMA24364-B1/B2-L            |
| Temperatura ambianta                 | -10 °C...60 °C               |
| Tipul de montare                     | insurubat fix                |
| Nota privind materialele             | Conform RoHS                 |
| Material sistem de actionare         | Otel galvanizat              |