


## Set paralel EAMM-U-86-S62-87A-102

Numar piesa: 8059032

**FESTO**



### Fisa de date

| Caracteristica               | Valoare               |
|------------------------------|-----------------------|
| Dimensiune                   | 86                    |
| Pozitie de instalare         | orice                 |
| Turatie max.                 | 5000 1/min            |
| Conformitatea LABS           | VDMA24364-B2-L        |
| Temperatura de depozitare    | -25 °C...60 °C        |
| Umiditate relativa           | 0 - 95 %              |
| Tip de protectie             | IP40                  |
| Temperatura ambianta         | -10 °C...60 °C        |
| Momentul de inertie al masei | 175 kgmm <sup>2</sup> |
| Cuplu de antrenare in gol    | 0.25 Nm               |
| Cuplu transmisibil           | 9.5 Nm                |
| Greutate produs              | 2500 g                |
| Cod de interfata actuator    | S62                   |
| Codul interfetei motor In    | 87A                   |
| Nota privind materialele     | Conform RoHS          |