


Set paralel EAMM-U-110-S62-84AA-207

Numar piesa: 8059057

FESTO



Fisa de date

Caracteristica	Valoare
Dimensiune	110
Pozitie de instalare	orice
Turatie max.	5000 1/min
Conformitatea LABS	VDMA24364-B2-L
Temperatura de depozitare	-25 °C...60 °C
Umiditate relativa	0 - 95 %
Tip de protectie	IP40
Temperatura ambianta	-10 °C...60 °C
Momentul de inertie al masei	799 kgmm ²
Cuplu de antrenare in gol	0.3 Nm
Cuplu transmisibil	9.5 Nm
Greutate produs	6900 g
Cod de interfata actuator	S62
Codul interfetei motor In	84AA
Nota privind materialele	Conform RoHS