

Set paralel EAMM-U-145-S62-126AA-288

Numar piesa: 8059073

FESTO



Fisa de date

Caracteristica	Valoare
Dimensiune	145
Pozitie de instalare	orice
Turatie max.	4000 1/min
Conformitatea LABS	VDMA24364-B2-L
Temperatura de depozitare	-25 °C...60 °C
Umiditate relativa	0 - 95 %
Tip de protectie	IP40
Temperatura ambianta	-10 °C...60 °C
Momentul de inertie al masei	2270 kgmm ²
Cuplu de antrenare in gol	2 Nm
Cuplu transmisibil	9.5 Nm
Greutate produs	15000 g
Cod de interfata actuator	S62
Codul interfetei motor In	126AA
Nota privind materialele	Conform RoHS