

Prize de cuplare NPHS-D6-P-G38F

Numar piesa: 8059272

FESTO



Fisa de date

Caracteristica	Valoare
Latimea nominala	10.5 mm
Presiune de functionare interval complet de temperatura	-0.095 MPa...1.2 MPa -0.95 bar...12 bar -13.775 psi...174 psi
Debit nominal standard (normalizat conform DIN 1343)	1203 l/min...2083 l/min
Debitul nominal standardizat conform ISO 8778	1304.1 l/min...2258 l/min
Mediu de operare	Aer comprimat conform ISO 8573-1:2010 [7:::]
Nota referitoare la mediul de lucru/comanda	Este posibila functionarea cu ulei
Clasa de rezistenta la coroziune KBK	1 - stres redus la coroziune
Conformitatea LABS	VDMA24364-B1/B2-L
Temperatura ambianta	-10 °C...60 °C
Greutate produs	114 g
Conector pneumatic 1	Filet interior G3/8
Nota privind materialele	Conform RoHS
Material garnituri	NBR
Material arc	otel inoxidabil aliaj inalt
Material carcasa	Alama, nichelata
Material piesa filetata	Alama, nichelata
Material inel interior	POM
Material bila	otel inoxidabil inalt aliat
Material stifturi	Otel inalt aliat, inoxidabil
Material corp ventil	Alama
Manson de deblocare a materialului	POM PP Otel inalt aliat, inoxidabil