

Prize de cuplare NPHS-D6-M-G14

Numar piesa: 8059275

FESTO



Fisa de date

Caracteristica	Valoare
Latimea nominala	8.2 mm
Presiune de functionare interval complet de temperatura	-0.095 MPa...1.2 MPa -0.95 bar...12 bar -13.775 psi...174 psi
Debit nominal standard (normalizat conform DIN 1343)	1750 l/min...1833 l/min
Debitul nominal standardizat conform ISO 8778	1897 l/min...1987 l/min
Mediu de operare	Aer comprimat conform ISO 8573-1:2010 [7:-:-]
Nota referitoare la mediul de lucru/comanda	Este posibila functionarea cu ulei
Clasa de rezistenta la coroziune KBK	1 - stres redus la coroziune
Conformitatea LABS	VDMA24364-B1/B2-L
Temperatura ambianta	-20 °C...80 °C
Cuplu de strangere nominal	7 Nm
Toleranta fata de cuplul de strangere nominal	± 20 %
Greutate produs	173 g
Conector pneumatic 1	Filet exterior G1/4
Nota privind materialele	Conform RoHS
Material garnituri	NBR
Material arc	otel inoxidabil aliaj inalt
Material carcasa	Alama, nichelata
Material garnitura de filet	Aluminiu HNBR
Material piesa filetata	Alama, nichelata
Material manson	Aliaj de aluminiu forjat anodizat incolor
Material inel interior	Alama
Material bila	otel inoxidabil inalt aliat
Manson de deblocare a materialului	Alama, nichelata