

Tub plastic PTFEN-1/4-NT-300

Numar piesa: 8061181

FESTO



Fisa de date

Caracteristica	Valoare
Ø exterior Inch	1/4
raza de indoire relevanta pentru debit	40 mm
Ø interior	4.1 mm
Raza min. de indoire	37 mm
Nota de aplicare	Furtun fara imprimare
Presiune de functionare interval complet de temperatura	-0.095 MPa...0.5 MPa -0.95 bar...5 bar -13.775 psi...72.5 psi
Presiune de lucru in functie de temperatura	-0.095 MPa...1.2 MPa -0.95 bar...12 bar -13.775 psi...174 psi
Mediu de operare	Aer comprimat conform ISO 8573-1:2010 [7:-:-]
Material de testare la foc	UL94 V-0
Conformitatea LABS	VDMA24364-B2-L
Clasa de puritate a incaperii	Element instalat static, fara posibilitate de evaluare semnificativa conform ISO 14644-1
Siguranta alimentara	vedeti informatii detaliate despre material
Temperatura ambianta	-20 °C...150 °C
Greutatea produsului in functie de lungime	0.04 kg/m
Conexiune pneumatica	pentru conector cu Ø exterior 1/4"
Culoare	natura
Duritate Shore	D 55 +/-5
Nota privind materialele	Conform RoHS
Material furtun	PTFE