

## Tub plastic PTFEN-1/2-NT-150

Numar piesa: 8061183

FESTO



### Fisa de date

| Caracteristica                                          | Valoare                                                                                  |
|---------------------------------------------------------|------------------------------------------------------------------------------------------|
| Ø exterior Inch                                         | 1/2                                                                                      |
| raza de indoire relevanta pentru debit                  | 120 mm                                                                                   |
| Ø interior                                              | 8.5 mm                                                                                   |
| Raza min. de indoire                                    | 81 mm                                                                                    |
| Nota de aplicare                                        | Furtun fara imprimare                                                                    |
| Presiune de functionare interval complet de temperatura | -0.095 MPa...0.5 MPa<br>-0.95 bar...5 bar<br>-13.775 psi...72.5 psi                      |
| Presiune de lucru in functie de temperatura             | -0.095 MPa...1.2 MPa<br>-0.95 bar...12 bar<br>-13.775 psi...174 psi                      |
| Mediu de operare                                        | Aer comprimat conform ISO 8573-1:2010 [7:-:-]                                            |
| Material de testare la foc                              | UL94 V-0                                                                                 |
| Conformitatea LABS                                      | VDMA24364-B2-L                                                                           |
| Clasa de puritate a incaperii                           | Element instalat static, fara posibilitate de evaluare semnificativa conform ISO 14644-1 |
| Siguranta alimentara                                    | vedeti informatii detaliate despre material                                              |
| Temperatura ambianta                                    | -20 °C...150 °C                                                                          |
| Greutatea produsului in functie de lungime              | 0.153 kg/m                                                                               |
| Conexiune pneumatica                                    | pentru conector cu Ø exterior 1/2"                                                       |
| Culoare                                                 | natura                                                                                   |
| Duritate Shore                                          | D 55 +/-5                                                                                |
| Nota privind materialele                                | Conform RoHS                                                                             |
| Material furtun                                         | PTFE                                                                                     |