


Set axial EAMM-A-L27-60RA

Numar piesa: 8063452

FESTO



Fisa de date

Caracteristica	Valoare
Lungime nominala	32.1 mm
Pozitie de instalare	orice
Turatie max.	10000 1/min
Conformitatea LABS	VDMA24364-B2-L
Temperatura de depozitare	-25 °C...60 °C
Umiditate relativa	0 - 95 %
Tip de protectie	IP40
Temperatura ambianta	-10 °C...60 °C
Momentul de inertie al masei	0.45 kgmm ²
Cuplu transmisibil	2 Nm
Greutate produs	298 g
Cod de interfata actuator	L27
Codul interfetei motor In	60RA
Nota privind materialele	Conform RoHS