


Set axial EAMM-A-L95-90GA

Numar piesa: 8063526

FESTO



Fisa de date

Caracteristica	Valoare
Lungime nominala	71.4 mm
Pozitie de instalare	orice
Turatie max.	4500 1/min
Conformitatea LABS	VDMA24364-B2-L
Temperatura de depozitare	-25 °C...60 °C
Umiditate relativa	0 - 95 %
Tip de protectie	IP40
Temperatura ambianta	-10 °C...60 °C
Momentul de inertie al masei	374 kgmm ²
Cuplu transmisibil	133 Nm
Greutate produs	2834 g
Cod de interfata actuator	L95
Codul interfetei motor In	90GA
Nota privind materialele	Conform RoHS