


Set axial EAMM-A-N48-120GA

Numar piesa: 8063605

FESTO



Fisa de date

Caracteristica	Valoare
Lungime nominala	58.5 mm
Pozitie de instalare	orice
Turatie max.	6000 1/min
Conformitatea LABS	VDMA24364-B2-L
Temperatura de depozitare	-25 °C...60 °C
Umiditate relativa	0 - 95 %
Tip de protectie	IP40
Temperatura ambianta	-10 °C...60 °C
Momentul de inertie al masei	39 kgmm ²
Cuplu transmisibil	17 Nm
Greutate produs	1091 g
Cod de interfata actuator	N48
Codul interfetei motor In	120GA
Nota privind materialele	Conform RoHS