


Set axial EAMM-A-N80-75GA

Numar piesa: 8063609

FESTO



Fisa de date

Caracteristica	Valoare
Lungime nominala	78.5 mm
Pozitie de instalare	orice
Turatie max.	5500 1/min
Conformitatea LABS	VDMA24364-B2-L
Temperatura de depozitare	-25 °C...60 °C
Umiditate relativa	0 - 95 %
Tip de protectie	IP40
Temperatura ambianta	-10 °C...60 °C
Momentul de inertie al masei	151 kgmm ²
Cuplu transmisibil	47 Nm
Greutate produs	1692 g
Cod de interfata actuator	N80
Codul interfetei motor In	75GA
Nota privind materialele	Conform RoHS