

Suport amortizor soc DAYP-L8-40

Numar piesa: 8069008

FESTO



Fisa de date

Caracteristica	Valoare
Dimensiune	40
Pozitie de instalare	orice
Clasa de rezistenta la coroziune KBK	1 - stres redus la coroziune
Conformitatea LABS	VDMA24364-B1/B2-L
Temperatura ambianta	0 °C...60 °C
Greutate produs	560 g
Tipul de montare	cu orificiu de trecere
Nota privind materialele	Conform RoHS fara cupru
Opriri de material	otel inoxidabil aliaj inalt
Material surub de prindere	Otel, galvanizat
Material piulita	Otel, galvanizat