

## Niplu reductor NPFC-R-G12-G14-MF-P50

Numar piesa: 8069232

**FESTO**



### Fisa de date

| Caracteristica                       | Valoare                                       |
|--------------------------------------|-----------------------------------------------|
| Material racord filetat              | Alama, nichelata                              |
| Unitate de ambalare                  | 50                                            |
| Presiune de lucru                    | -0.95 bar...50 bar                            |
| Mediu de operare                     | Aer comprimat conform ISO 8573-1:2010 [-:::-] |
| Clasa de rezistenta la coroziune KBK | 1 - stres redus la coroziune                  |
| Conformitatea LABS                   | VDMA24364-B1/B2-L                             |
| Temperatura ambianta                 | -20 °C...150 °C                               |
| Greutate produs                      | 31.4 g                                        |
| Conector pneumatic 1                 | G1/2                                          |
| Conexiune pneumatica 2               | G1/4                                          |
| Nota privind materialele             | Conform RoHS                                  |