

# Ventuza vacuum OGVM-20X60-GV-N-G14F

Numar piesa: 8073862

FESTO



## Fisa de date

| Caracteristica                                             | Valoare                                                     |
|------------------------------------------------------------|-------------------------------------------------------------|
| Ventuza de compensare a inaltimii                          | 5 mm                                                        |
| Raza min. a piesei de prelucrat                            | 12.5 mm                                                     |
| Latimea nominala                                           | 6 mm                                                        |
| Dimensiunea ventuzei                                       | 20x60 mm                                                    |
| Volum de aspiratie                                         | 5 cm <sup>3</sup>                                           |
| Pozitie de conectare                                       | sus                                                         |
| Pozitie de instalare                                       | orice                                                       |
| Forma de ventuza                                           | forma ovala de clopot                                       |
| Presiune de lucru                                          | -95 kPa...0 kPa<br>-0.95 bar...0 bar<br>-13.775 psi...0 psi |
| Presiunea nominala de functionare                          | -60 kPa<br>-0.6 bar                                         |
| Mediu de operare                                           | aer atmosferic conform ISO 8573-1:2010 [7:-:-]              |
| Clasa de rezistenta la coroziune KBK                       | 2 - Solicitare moderata din cauza coroziunii                |
| Conformitatea LABS                                         | VDMA24364-A1-L                                              |
| Temperatura ambianta                                       | -20 °C...80 °C                                              |
| Fora de mentinere la presiune de lucru nominala            | 81 N                                                        |
| Fora transversala verticala la presiunea de lucru nominala | 103 N                                                       |
| Greutate produs                                            | 16 g                                                        |
| Tipul de montare                                           | prin racordul de vid                                        |
| Racord de vacuum                                           | Filet interior G1/4                                         |
| Culoare                                                    | negru                                                       |
| Duritate Shore                                             | 60 +/- 5                                                    |
| Material pivot de insurubare                               | Aliaj de aluminiu forjat                                    |
| Nota privind materialele                                   | Conform RoHS                                                |
| Material ventuze                                           | NBR                                                         |