

Set paralel EAMM-U-30-V20-28AA-44

Numar piesa: 8093176

FESTO



Fisa de date

Caracteristica	Valoare
Dimensiune	30
Centru	44 mm
Pozitie de instalare	orice
Raportul de transmisie	1:1
Turatie max.	3000 1/min
Conformitatea LABS	VDMA24364 zona III
Temperatura de depozitare	-20 °C...60 °C
Umiditate relativa	0 - 95 %
Tip de protectie	IP40
Temperatura ambianta	0 °C...50 °C
Momentul de inertie al masei	2.11 kgmm ²
Cuplu de antrenare in gol	0.015 Nm
Cuplu transmisibil	0.05 Nm
Greutate produs	94 g
Cod de interfata actuator	V20
Codul interfetei motor In	28AA
Nota privind materialele	Conform RoHS