

Capac de prindere formă DHAS-GA-B22-S

Numar piesa: 8097634

FESTO



Fisa de date

Caracteristica	Valoare
Executie capac de prindere forma	Standard
Nota referitoare la mediul de lucru/comanda	Aveti in vedere rezistenta materialelor in contact cu mediul
Conformitatea LABS	VDMA24364 zona III
Temperatura ambianta	-40 °C...180 °C
Fora teoretica la 0,6 MPa (6 bari, 87 psi), debit de retur	189 N
Fora teoretica la 0,6 MPa (6 bari, 87 psi), cursa de avans	158 N
Greutate produs	18 g
Nota privind materialele	Conform RoHS
Material capac	VMQ (silicon)