


Cuplaj
EAMC-42-50-12-16-U
Numar piesa: 8099433

FESTO



Fisa de date

Caracteristica	Valoare
Diametrul de montare 1	12 mm
Diametru de montare 2	16 mm
Dimensiune	42
Lungime nominala	50 mm
Pozitie de instalare	orice
Turatie max.	6000 1/min
Conformitatea LABS	VDMA24364-B2-L
Temperatura de depozitare	-25 °C...60 °C
Umiditate relativa	0 - 95 %
Temperatura ambianta	-25 °C...60 °C
Momentul de inertie al masei	34.8 kgmm ²
Cuplu transmisibil	21 Nm
Greutate produs	141 g
Nota privind materialele	Conform RoHS