


Set paralel EAMM-U-70-S48-60R-96

Numar piesa: 8105843

FESTO



Fisa de date

Caracteristica	Valoare
Dimensiune	70
Pozitie de instalare	orice
Turatie max.	5000 1/min
Conformitatea LABS	VDMA24364-B2-L
Temperatura de depozitare	-25 °C...60 °C
Umiditate relativa	0 - 95 %
Tip de protectie	IP40
Temperatura ambianta	-10 °C...60 °C
Momentul de inertie al masei	118 kgmm ²
Cuplu de antrenare in gol	0.18 Nm
Cuplu transmisibil	7 Nm
Greutate produs	1800 g
Cod de interfata actuator	S48
Codul interfetei motor In	60R
Nota privind materialele	Conform RoHS