

Set paralel EAMM-U-145-D80-90GA-188

Numar piesa: 8105897

FESTO



Fisa de date

Caracteristica	Valoare
Dimensiune	145
Pozitie de instalare	orice
Turatie max.	4000 1/min
Conformitatea LABS	VDMA24364-B2-L
Temperatura de depozitare	-25 °C...60 °C
Umiditate relativa	0 - 95 %
Tip de protectie	IP40
Temperatura ambianta	-10 °C...60 °C
Momentul de inertie al masei	2270 kgmm ²
Cuplu de antrenare in gol	2 Nm
Cuplu transmisibil	9.5 Nm
Greutate produs	12000 g
Cod de interfata actuator	D80
Codul interfetei motor In	90GA
Nota privind materialele	Conform RoHS