


Set axial
EAMM-A-D40-70AA

Numar piesa: 8105952

FESTO



Fisa de date

Caracteristica	Valoare
Pozitie de instalare	orice
Conformitatea LABS	VDMA24364-B2-L
Temperatura de depozitare	-25 °C...60 °C
Umiditate relativa	0 - 95 %
Tip de protectie	IP40
Temperatura ambianta	-10 °C...60 °C
Cuplu transmisibil	12.5 Nm
Greutate produs	443 g
Cod de interfata actuator	D40
Codul interfetei motor In	70AA 70AB
Nota privind materialele	Conform RoHS