

Clema de siguranta NPAP-QE-S-Q8-P10

Numar piesa: 8113230

FESTO



Fisa de date

Caracteristica	Valoare
Unitate de ambalare	10
Pozitie de instalare	orice
Presiune de functionare interval complet de temperatura	-0.095 MPa...0.8 MPa -0.95 bar...8 bar -13.775 psi...116 psi
Clasa de rezistenta la coroziune KBK	1 - stres redus la coroziune
Conformitatea LABS	VDMA24364 zona III
Clasa de puritate a incaperii	Element instalat static, fara posibilitate de evaluare semnificativa conform ISO 14644-1
Temperatura ambianta	-5 °C...60 °C
Greutate produs	0.11 g
Conexiune pneumatica	pentru furtun cu Ø exterior 8 mm
Nota privind materialele	Conform RoHS