

Cuplaj
EAMC-30-32-8-12
Numar piesa: 8115760

FESTO



Fisa de date

Caracteristica	Valoare
Diametrul de montare 1	8 mm
Diametru de montare 2	12 mm
Dimensiune	30
Lungime nominala	32 mm
Pozitie de instalare	orice
Turatie max.	8000 1/min
Conformitatea LABS	VDMA24364-B2-L
Temperatura de depozitare	-25 °C...60 °C
Umiditate relativa	0 - 95 %
Temperatura ambianta	-25 °C...60 °C
Momentul de inertie al masei	5.87 kgmm ²
Cuplu transmisibil	12.5 Nm
Greutate produs	48 g
Nota privind materialele	Conform RoHS