

Bobina VACC-S18-120-K4-2U-NE4ME

Numar piesa: 8118260

FESTO



Fisa de date

Caracteristica	Valoare
Tip de actionare	electric
Pozitie de instalare	orice
Indicatorul pozitiei de comutare	nu
Ciclu de lucru	100%
Clasa de izolare	H
Caracteristici bobina	110 V CA: 50/60 Hz, putere 12,0 VA 110 V CC: 12,0 W
Fluctuatii de tensiune admise	-15 % / +10 %
Protectie Ex certificata in afara UE	EPL Db (CN) EPL Gb (CN)
Protectie la explozie	Zona 1 (CN) Zona 21 (CN)
Organizatia emitenta a certificatului	GYJ23.1169X
Tip de protectie la explozie pentru gaz	Ex eb mb IIC T4 Gb
Tip de protectie contra exploziilor pentru praf	Ex tb IIIC T120°C Db
Temperatura ambientala Ex	T4, T120°C: -25°C ≤ Ta ≤ +40°C
Conformitatea LABS	VDMA24364 zona III
Tip de protectie	IP66
Greutate produs	580 g
Conector electric	Cutie de borne, filet de intrare cablu M20x1,5
Nota privind materialele	Conform RoHS