

Cuplaj
EAMD-42-48-16-16X25
Numar piesa: 8121126

FESTO



Fisa de date

Caracteristica	Valoare
Diametrul de montare 1	16 mm
Diametru de montare 2	16 mm
Dimensiune	42
Lungime nominala	48 mm
Pozitie de instalare	orice
Turatie max.	6000 1/min
Conformitatea LABS	VDMA24364-B2-L
Temperatura de depozitare	-25 °C...60 °C
Umiditate relativa	0 - 95 %
Temperatura ambianta	-25 °C...60 °C
Momentul de inertie al masei	45 kgmm ²
Cuplu transmisibil	17 Nm
Greutate produs	217 g
Nota privind materialele	Conform RoHS