

Echer fixare PAMP-MB-44

Numar piesa: 8123058

FESTO



Fisa de date

Caracteristica	Valoare
Dimensiune	44
Seria	P
Clasa de rezistenta la coroziune KBK	4 - Mediu coroziv deosebit de puternic
Conformitatea LABS	VDMA24364-B2-L
Cuplu de strangere max. la fixarea ventilului	2.5 Nm
Temperatura medie	-60 °C...80 °C
Temperatura ambianta	-60 °C...80 °C
Greutate produs	32 g
Nota privind materialele	Conform RoHS
Material suruburi	otel inoxidabil inalt aliat
Material echer	otel inoxidabil inalt aliat