


**Set axial**  
**EAMM-A-D50-84AA**

Numar piesa: 8123490

**FESTO**



**Fisa de date**

| Caracteristica            | Valoare        |
|---------------------------|----------------|
| Pozitie de instalare      | orice          |
| Conformitatea LABS        | VDMA24364-B2-L |
| Temperatura de depozitare | -25 °C...60 °C |
| Umiditate relativa        | 0 - 95 %       |
| Tip de protectie          | IP40           |
| Temperatura ambianta      | -10 °C...60 °C |
| Cuplu transmisibil        | 17 Nm          |
| Greutate produs           | 1012 g         |
| Cod de interfata actuator | D50            |
| Codul interfetei motor In | 84AA           |
| Nota privind materialele  | Conform RoHS   |