

**Suport
CAFM-D4-W**
Numar piesa: 8127358

FESTO



Fisa de date

Caracteristica	Valoare
Latime	216 mm
Inaltime	97 mm
Lungime	345 mm
Clasa de rezistenta la coroziune KBK	0 - nu este afectat de coroziune
Conformitatea LABS	VDMA24364 zona III
Temperatura de depozitare	-20 °C...70 °C
Temperatura ambianta	0 °C...40 °C
Greutate produs	749 g
Tipul de montare	insurubat
Nota privind materialele	Conform RoHS
Material echer de fixare	Otel acoperit cu pulbere