

Cuplaj
EAMC-56-58-22-24
Numar piesa: 8134826

FESTO



Fisa de date

Caracteristica	Valoare
Diametrul de montare 1	22 mm
Diametru de montare 2	24 mm
Dimensiune	56
Lungime nominala	58 mm
Pozitie de instalare	orice
Turatie max.	5500 1/min
Conformitatea LABS	VDMA24364-B2-L
Temperatura de depozitare	-25 °C...60 °C
Umiditate relativa	0 - 95 %
Temperatura ambianta	-25 °C...60 °C
Momentul de inertie al masei	129 kgmm ²
Cuplu transmisibil	60 Nm
Greutate produs	274 g
Nota privind materialele	Conform RoHS