

Indicator pozitie SASF-S2-B-V-A20

Numar piesa: 8140395

FESTO



Fisa de date

Caracteristica	Valoare
Domeniu de reglaj unghi de pivotare	0 grd...360 grd
Functii suplimentare	maneta de actionare reglabila
Dimensiuni l x L x H	Ø 65 x 48,5
Rezistenta la vibratii	Testul aplicatiei de transport cu grad de inclinare 2 conform FN 942017-4 si EN 60068-2-6
Rezistenta la socuri	Test de soc cu grad de inclinare 2 conform FN 942017-5 si EN 60068-2-27
Conformitatea LABS	VDMA24364 zona III
Temperatura ambianta	-25 °C...70 °C
Greutate produs	96 g
Tipul de montare	conform VDI/VDE 3845
Culoarea carcasei	negru
Nota privind materialele	Conform RoHS
Material element de distantare	PA
Material carcasa	PA PP otel inoxidabil inalt aliat
Material suruburi	otel inoxidabil inalt aliat