

Amortizor de zgomot UO-M5

Numar piesa: 8141085

FESTO



Fisa de date

Caracteristica	Valoare
Pozitie de instalare	orice
Structura constructiva	Amortizor de zgomot deschis
Presiune de lucru	0 MPa...0.8 MPa 0 bar...8 bar
Mediu de operare	Aer comprimat conform ISO 8573-1:2010 [7:4:4]
Conformitatea LABS	VDMA24364-B1/B2-L
Temperatura ambianta	-10 °C...60 °C
Greutate produs	0.5 g
Conexiune pneumatica	M5
Material insertie amortizor de zgomot	PE
Material pivot de insurubare	PE
Nota privind materialele	Conform RoHS