


Angrenaj|cutie de viteze|reductor|transmisie
EMGA-40-P-G12-EAS-40

Numar piesa: 8141730

FESTO



Fisa de date

Caracteristica	Valoare
Dimensiunea flansei reductorului	40 mm
Dimensiune flansa motor	40 mm
Joc de rasucire	0.31 grd
Tipul de reductor	Reductor planetar
Raportul de transmisie	12:1
Turatie de lucru max.	18000 1/min
Temperatura de functionare unitate actionare	-25 °C...90 °C
Conformitatea LABS	VDMA24364-B2-L
Tip de protectie	IP54
Cuplu de iesire continuu	20 Nm
Momentul de inertie al reductorului	0.025 kgcm ²
Cuplu de iesire max.	32 Nm
Randament max.	96 %
Rigiditate la torsiune	1 Nm/arcmin
Greutate produs	450 g
Interfata de iesire la unitatea de actionare	40G
Interfata reductor unitate de actionare	40P
Nota privind materialele	Conform RoHS