


Angrenaj|cutie de viteze|reductor|transmisie
EMGA-120-P-G12-SAS-140

Numar piesa: 8141760

FESTO



Fisa de date

Caracteristica	Valoare
Dimensiunea flansei reductorului	120 mm
Dimensiune flansa motor	140 mm
Joc de rasucire	0.15 grd
Tipul de reductor	Reductor planetar
Raportul de transmisie	12:1
Turatie de lucru max.	6500 1/min
Temperatura de functionare unitate actionare	-25 °C...90 °C
Conformitatea LABS	VDMA24364-B2-L
Tip de protectie	IP54
Cuplu de iesire continuu	260 Nm
Momentul de inertie al reductorului	2.224 kgcm ²
Cuplu de iesire max.	520 Nm
Randament max.	96 %
Rigiditate la torsiune	22 Nm/arcmin
Greutate produs	9000 g
Interfata de iesire la unitatea de actionare	120G
Interfata reductor unitate de actionare	140A
Nota privind materialele	Conform RoHS