


Angrenaj|cutie de viteze|reductor|transmisie
EMGA-60-P-G8-SST-57

Numar piesa: 8141764

FESTO



Fisa de date

Caracteristica	Valoare
Dimensiunea flansei reductorului	60 mm
Dimensiune flansa motor	57 mm
Joc de rasucire	0.17 grd
Tipul de reductor	Reductor planetar
Raportul de transmisie	8:1
Turatie de lucru max.	13000 1/min
Temperatura de functionare unitate actionare	-25 °C...90 °C
Conformitatea LABS	VDMA24364-B2-L
Tip de protectie	IP54
Cuplu de iesire continuu	18 Nm
Momentul de inertie al reductorului	0.067 kgcm ²
Cuplu de iesire max.	29 Nm
Randament max.	97 %
Rigiditate la torsiune	2.4 Nm/arcmin
Greutate produs	900 g
Interfata de iesire la unitatea de actionare	60G
Interfata reductor unitate de actionare	57A
Nota privind materialele	Conform RoHS