

Șurub de închidere NETC-P-M20-PBK-T14

Numar piesa: 8151591

FESTO



Fisa de date

Caracteristica	Valoare
Temperatura ambianta	-40 °C...100 °C
Tip de protectie	IP66 IP68
Nota privind tipul de protectie	IP68 la 5 bari timp de 30 de minute
Marca CE (consultati Declaratia de conformitate)	conform directivei RoHS a UE
Dimensiune	M20x1,5
Culoare	negru
Material presetupa	PA
Material garnituri	EPDM
Greutate produs	2 g
Unitate de ambalare	1
Conformitatea LABS	VDMA24364 zona III
Nota privind materialele	Conform RoHS