

**Bobina**  
**VACC-S13-18-K4-2U-KS4ME**  
Numar piesa: 8156760

**FESTO**



**Fisa de date**

| Caracteristica                                  | Valoare                                                                                                |
|-------------------------------------------------|--------------------------------------------------------------------------------------------------------|
| Tip de actionare                                | electric                                                                                               |
| Pozitie de instalare                            | orice                                                                                                  |
| Indicatorul pozitiei de comutare                | nu                                                                                                     |
| Ciclu de lucru                                  | 100%                                                                                                   |
| Clasa de izolare                                | H                                                                                                      |
| Caracteristici bobina                           | 110 V CC: 1,8 W<br>110 V CA: 40/65 Hz, putere 1,8 VA                                                   |
| Fluctuatii de tensiune admise                   | -15 % / +10 %                                                                                          |
| Protectie Ex certificata in afara UE            | EPL Db (KR)<br>EPL Gb (KR)                                                                             |
| Protectie la explozie                           | Zona 1 (KR)<br>Zona 21 (KR)                                                                            |
| Organizatia emitenta a certificatului           | 21-AV4BO-0279X<br>22-AV4BO-0051X                                                                       |
| Tip de protectie la explozie pentru gaz         | Ex e mb IIC T4, T5, T6                                                                                 |
| Tip de protectie contra exploziilor pentru praf | Ex tD A21 IP65 T85/T95/T130°C                                                                          |
| Temperatura ambientala Ex                       | T4, T130°C: -30°C <= Ta <= +60°C<br>T5, T95°C: -30°C <= Ta <= +60°C<br>T6, T85°C: -30°C <= Ta <= +50°C |
| Conformitatea LABS                              | VDMA24364 zona III                                                                                     |
| Tip de protectie                                | IP65                                                                                                   |
| Greutate produs                                 | 330 g                                                                                                  |
| Conector electric                               | Cutie de borne, filet de intrare cablu M20x1,5                                                         |
| Nota privind materialele                        | Conform RoHS                                                                                           |