

Bobina
VACC-S13-18-K4-27U-KS4ME
Numar piesa: 8156763

FESTO



Fisa de date

Caracteristica	Valoare
Tip de actionare	electric
Pozitie de instalare	orice
Indicatorul pozitiei de comutare	nu
Ciclu de lucru	100%
Clasa de izolare	H
Caracteristici bobina	60 V CA: 40/65 Hz, putere 1,8 VA 60 V CC: 1,8 W
Fluctuatii de tensiune admise	-15 % / +10 %
Protectie Ex certificata in afara UE	EPL Db (KR) EPL Gb (KR)
Protectie la explozie	Zona 1 (KR) Zona 21 (KR)
Organizatia emitenta a certificatului	21-AV4BO-0279X 22-AV4BO-0051X
Tip de protectie la explozie pentru gaz	Ex e mb IIC T4, T5, T6
Tip de protectie contra exploziilor pentru praf	Ex tD A21 IP65 T85/T95/T130°C
Temperatura ambientala Ex	T4, T130°C: -30°C <= Ta <= +60°C T5, T95°C: -30°C <= Ta <= +60°C T6, T85°C: -30°C <= Ta <= +50°C
Conformitatea LABS	VDMA24364 zona III
Tip de protectie	IP65
Greutate produs	330 g
Conector electric	Cutie de borne, filet de intrare cablu M20x1,5
Nota privind materialele	Conform RoHS