

## Set de racordare DADG-AK-G8-20-125

Numar piesa: 8159796

**FESTO**



### Fisa de date

| Caracteristica                                 | Valoare                                                  |
|------------------------------------------------|----------------------------------------------------------|
| Dimensiune                                     | 20                                                       |
| Cursa                                          | 125 mm                                                   |
| Presiune de lucru                              | 0.1 MPa...0.8 MPa<br>1 bar...8 bar<br>14.5 psi...116 psi |
| Mediu de operare                               | Aer comprimat conform ISO 8573-1:2010 [7:4:4]            |
| Clasa de rezistenta la coroziune KBK           | 1 - stres redus la coroziune                             |
| Conformitatea LABS                             | VDMA24364-B1/B2-L                                        |
| Temperatura ambianta                           | -10 °C...60 °C                                           |
| Cuplu de strangere max.                        | 3 Nm                                                     |
| Toleranta, cuplu de strangere                  | ± 10 %                                                   |
| Cuplu de strangere max. conexiune pneumatica 1 | 3 Nm                                                     |
| Greutate produs                                | 54.2 g                                                   |
| Conexiune pneumatica                           | G1/8                                                     |
| Material adaptor                               | Rasina epoxidica                                         |
| Material garnituri                             | FPM                                                      |
| Material suruburi                              | Otel, acoperit                                           |