

Amortizor de soc DYSD-Q11-25-24-Y1F-L-Y10

Numar piesa: 8161534

FESTO



Fisa de date

Caracteristica	Valoare
Dimensiune	25
Cursa	24 mm
Amortizare	autoreglare
Pozitie de instalare	orice
Detectarea pozitiei	fara
Viteza max. de impact	1 m/s
Timp de resetare la temperatura camerei	0.3 s
Mod de functionare	cu apasare cu simpla actiune
Clasa de rezistenta la coroziune KBK	2 - Solicitare moderata din cauza coroziunii
Conformitatea LABS	VDMA24364-B2-L
Temperatura ambianta	0 °C...60 °C
Lungime de amortizare	24 mm
Forta max. de ridicare	4000 N
Consumul max. de energie pe cursa	180 J
Consum max. de energie pe ora	150000 J
Energie reziduala max.	0.8 J
Forta de restabilire	120 N
Forta minima de insertie	430 N
Greutate produs	635 g
Tipul de montare	cu piulita de blocare
Nota privind materialele	Conform RoHS
Material garnituri	NBR
Material carcasa	Otel galvanizat
Material tija de piston	otel aliaj inalt
Material piulita	Otel, galvanizat